

WN0cmIjYWwtb3V0bGV0cy9kdXBsZXguYXNweGQWAmYPFglfAAV6PGltZyByZXBsYWNIPSJkc3JliBkc3JjPSlvi9tZWRpYS9FQ0Q3QzY3NjAyQUQ0N



designed to be better.

 Search

Decorator Openings, One Gang, 302 Stainless Steel

SS26

Smooth Metal Wall Plate 1gang Decorator 302 Stainless Steel

Where to buy

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Type 302 Stainless Steel, non-magnetic: .032" nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Top 5 Resources

specifications

General Info

- Size: Standard
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121704
- U R: No

Technical Information

- Material: 302 Stainless Steel
- Capacity: 1-gang

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



resources

CUTSHEET