

9+L21IZGIhL0JGMEQ2NzA1Njk5MTQ4OTICQTBGQzQwQ0FENDYzMTk5LmFzaHgilGFsdD0iQWNjZXNzb3JpZXMgYW5kiENvbm5lY3RvcnMilHdpZHR



designed to be better.
Search

Toggle Switch Openings, Two Gang, 302 Stainless Steel

SS2
Smooth Metal Wall Plate 2gang Toggle 302 Stainless Steel

Submit Query
Where to buy Enter Postal Code Submit Query 0 Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Type 302 Stainless Steel, non-magnetic: .032" nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Top 5 Resources

- Stainless Steel Wall Plates, SF2502R1 (Cutsheet)

specifications

General Info

- Size: Standard
- Type: Toggle

Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121704
- U R: No

Dimensions

- Weight: 0.20262

Technical Information


- Material: 302 Stainless Steel
- Capacity: 2-gang

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



resources
CUTSHEET

 [Stainless Steel Wall Plates, SF2502R1PDF \(367.16kb\)](#)