

URCRDZGLmFzaHgilGFsdD0iUGx1Z21vbGQilHdpZHRoPSlyMTgilGhlaWdodD0iMTEyIiAvPjwvYT4gPGEgaWQ9ImN0bDA1X01haW50YXYxX2N0bDA



designed to be better.

 Search

## Toggle Switch Openings, Four Gang, 302 Stainless Steel

SS4

Smooth Metal Wall Plate 4gang Toggle 302 Stainless Steel

Where to buy 


0



Representative image shown.

- SPECIFICATIONS

### features & benefits

- Type 302 Stainless Steel, non-magnetic: .032" nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

### specifications

#### General Info

- Size: Standard
- Type: Toggle

#### Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121704
- U R: No

#### Dimensions

- Weight: 0.35674

#### Technical Information

- Material: 302 Stainless Steel
- Capacity: 4-gang

#### Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant

