

MDVfTWfPbk5hdjFfy3RsMDFfcnB0UmVzaWRlbnRpYWxfY3RsMTNfcnB0UmVzaWRlbnRpYWxTdWJtZW51X2N0bDAX2hsVmllld0xpbnmsilGNsYXNzP'



designed to be better.

[Search](#)

Duplex Receptacle Openings, One Gang, 302 Stainless Steel

SS8

Smooth Metal Wall Plate 1gang Duplex 302 Stainless Steel

[Submit Query](#)Where to buy [Submit Query](#)

0



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Type 302 Stainless Steel, non-magnetic: .032" nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)
- [Stainless Steel Wall Plates, SF2502R1 \(Cutsheet\)](#)

specifications

General Info

- Size: Standard
- Type: Duplex

Listing Agencies/Third Party Information

- cU Rus: No
- U N SPS C: 39121704

Technical Information

- Material: 302 Stainless Steel
- Capacity: 1-gang

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



resources BROCHURE

- [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

- [Stainless Steel Wall Plates, SF2502R1PDF \(367.16kb\)](#)