

GxSZXNpZGVudGlhbFN1YkxpbmsilGhyZWY9li93YWxsLXBsYXRlcy9zcGVjaWFsdHkuYXNweCI+U3BIY2lhbHR5IFdhdGwUGxhdGVzICYgQWNjZXNzI



designed to be better.

Search

Screwless Decorator Openings, Metal Subplate, Two Gang, White

SW262W

Screwless Wall Plate 2gang Decorator Metal Subplate White

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Screwless Decorator Openings, Metal Subplate, Two Gang, Brown



Screwless Decorator Openings, Metal Subplate, Two Gang, Black



Screwless Decorator Openings, Metal Subplate, Two Gang, Gray



Screwless Decorator Openings, Metal Subplate, Two Gang, Ivory



Screwless Decorator Openings, Metal Subplate, Two Gang, Light Almond

- SPECIFICATIONS
- RESOURCES

features & benefits

- Molded of .065" thick polycarbonate with matte finish.
- 2-piece plastic subplate made of polycarbonate ("SWP" Series only).
- Metal subplate made of .042" zinc-plated steel ("SW" Series only).
- Extra 1/8" width and height than Standard size plates.

- Available in Ivory, White, Brown, Gray, Black, and Light Almond.
- Oversized opening to accommodate all NEMA 26 decorator-style openings.

Top 5 Resources

-  [Screwless Wall Plates \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Color: White
- Type: Screwless
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cJ Lus: Yes
- cJ Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121704
- U R: No

Dimensions

- Height U S: 4.87"
- Width U S: 4.912"

Technical Information

- Material: Metal
- Capacity: 2-Gang


Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



resources

BROCHURE

-  [Screwless Wall PlatesPDF \(749.69kb\)](#)
-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)