

b3RIY3RvcnMgJiBQb3dlciBTdHJpcHM8L2E+IDx1bCBjbGFzc3R1uZXCiPiA8bGkgY2xhc3M9ImNvbDliPiA8YSBpZD0iY3RsMDVFTWFpbk5hdjFFY:



designed to be better.

Search

Screwless Decorator Openings, Metal Subplate, Four Gang, White

SW264W

Screwless Wall Plate 4gang Decorator Metal Subplate White

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Screwless Decorator Openings, Metal Subplate, Four Gang, Brown



Screwless Decorator Openings, Metal Subplate, Four Gang, Black



Screwless Decorator Openings, Metal Subplate, Four Gang, Gray



Screwless Decorator Openings, Metal Subplate, Four Gang, Ivory



Screwless Decorator Openings, Metal Subplate, Four Gang, Light Almond

- SPECIFICATIONS
- RESOURCES

features & benefits

- Molded of .065" thick polycarbonate with matte finish.
- 2-piece plastic subplate made of polycarbonate ("SWP" Series only).
- Metal subplate made of .042" zinc-plated steel ("SW" Series only).
- Extra 1/8" width and height than Standard size plates.

- Available in Ivory, White, Brown, Gray, Black, and Light Almond.
- Oversized opening to accommodate all NEMA 26 decorator-style openings.

Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Screwless Wall Plates (Brochure)

specifications

General Info

- Color: White
- Type: Screwless
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cJ Lus: Yes
- cJ Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121704
- U R: No

Dimensions

- Height U S: 4.87"
- Width U S: 8.536"

Technical Information



- Material: Metal
- Capacity: 4-Gang

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
-



resources BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)
-  Screwless Wall PlatesPDF (749.69kb)