


TM818TRWCC



TM838TRLACC

Switches

TradeMaster® Tamper-Resistant Decorator Combination Switches

15A, 120/125VAC

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				UL ₂₀	UL ₄₉₈	cUL _{us}
Tamper-Resistant Single Pole Switch & Single Receptacle						
TM818TRICC	15 120/125	Ivory	5-15R	•	•	•
TM818TRWCC	15 120/125	White	5-15R	•	•	•
TM818TRCC	15 120/125	Brown	5-15R	•	•	•
TM818TRBKCC	15 120/125	Black	5-15R	•	•	•
TM818TRLACC	15 120/125	Light Almond	5-15R	•	•	•
Tamper-Resistant Single Pole Switch & Single Receptacle with Pilot Light						
TM818TRPLICC	15 120/125	Ivory	5-15R	•	•	•
TM818TRPLWCC	15 120/125	White	5-15R	•	•	•
TM818TRPLBKCC	15 120/125	Black	5-15R	•	•	•
TM818TRPLLACC	15 120/125	Light Almond	5-15R	•	•	•
Tamper-Resistant Three-Way Switch & Single Receptacle						
TM838TRICC	15 120/125	Ivory	5-15R	•	•	•
TM838TRWCC	15 120/125	White	5-15R	•	•	•
TM838TRCC	15 120/125	Brown	5-15R	•	•	•
TM838TRBKCC	15 120/125	Black	5-15R	•	•	•
TM838TRLACC	15 120/125	Light Almond	5-15R	•	•	•
Tamper-Resistant Two Single Pole Switches & Single Receptacle						
TM8118TRICC	15 120/125	Ivory	5-15R	•	•	•
TM8118TRWCC	15 120/125	White	5-15R	•	•	•
TM8118TRCC	15 120/125	Brown	5-15R	•	•	•
TM8118TRBKCC	15 120/125	Black	5-15R	•	•	•
TM8118TRLACC	15 120/125	Light Almond	5-15R	•	•	•