


Switches TradeMaster® Decorator Illuminated & Self-Grounding Switches

15A, 120 & 120/277VAC



Features	
<ul style="list-style-type: none"> ■ Designer-style satin-finish rocker. ■ High-impact resistant thermoplastic construction. ■ External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG. ■ Push wire #14 AWG. ■ Narrow back body leaves more room for wires in the box. 	<ul style="list-style-type: none"> ■ Extra-long, through-body strap eliminates floating installations and imperfect applications. ■ Smooth, quiet paddle action. ■ Easy-access green hex head ground screw. ■ Tri-drive ground, terminal and mounting screws. ■ Self-grounding models provide automatic ground clip.



TM870LASL



TM870SLA

Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL 20	C22.2 111
Single Pole Illuminated Decorator Switches Grounding (Lighted when OFF)				
TM870ISL	15 120	Ivory	•	•
TM870WSL	15 120	White	•	•
TM870LASL	15 120	Light Almond	•	•
Self-Grounding Single Pole Decorator Switches				
TM870SI	15 120/277	Ivory	•	•
TM870SW	15 120/277	White	•	•
TM870S	15 120/277	Brown	•	•
TM870SBK	15 120/277	Black	•	•
TM870SLA	15 120/277	Light Almond	•	•
Three-Way Illuminated Decorator Switches Grounding (Lighted when OFF)				
TM873ISL	15 120	Ivory	•	•
TM873WSL	15 120	White	•	•
TM873LASL	15 120	Light Almond	•	•
Self-Grounding Three-Way Decorator Switches				
TM873SI	15 120/277	Ivory	•	•
TM873SW	15 120/277	White	•	•
TM873S	15 120/277	Brown	•	•
TM873SBK	15 120/277	Black	•	•
TM873SLA	15 120/277	Light Almond	•	•
Four-Way Illuminated Decorator Switches Grounding (Lighted when OFF)				
TM874ISL	15 120	Ivory	•	•
TM874WSL	15 120	White	•	•
TM874LASL	15 120	Light Almond	•	•
Self-Grounding Four-Way Decorator Switches				
TM874SI	15 120/277	Ivory	•	•
TM874SW	15 120/277	White	•	•
TM874S	15 120/277	Brown	•	•
TM874SBK	15 120/277	Black	•	•
TM874SLA	15 120/277	Light Almond	•	•

All devices listed on this page conform to NEMA WD-1 and WD-6.