



designed to be better.

Search

Toggle Switch Openings, Two Gang, Ivory

TP2I

Trademaster Wall Plate, double gang and toggle plate, is molded of rugged, practically indestructible self-extinguishing nylon. It is preferred for hospital, industrial, institutional, and other high-abuse applications. Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Toggle Switch Openings, Two Gang, White





Toggle Switch Openings, Two Gang, Brown



Toggle Switch Openings, Two Gang, Black



Toggle Switch Openings, Two Gang, Gray



Toggle Switch Openings, Two Gang, Light Almond



Toggle Switch Openings, Two Gang, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Nominal thickness, .070 inch.

Top 5 Resources

-  [TradeMaster Thermoplastic Nylon Wall Plates, SF2501R1 \(Cutsheet\)](#)

specifications

General Info

- Color: Ivory
- Size: Standard
- Type: Toggle

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121704
- U R: No

Dimensions

- Weight: 0.0953

Technical Information

- Material: Plastic
- Capacity: 2-gang


Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
-



resources

CUTSHEET

 [TradeMaster Thermoplastic Nylon Wall Plates, SF2501R1PDF \(353.88kb\)](#)