



designed to be better.

Blank Plates -- Box Mounted, Two Gang, Gray

TP23GRY

Trademaster Plate 2gang Blank Box Mount Gray

Where to buy

0



Representative image shown.

AVAILABLE OPTIONS



Blank Plates -- Box Mounted, Two Gang, White





Blank Plates -- Box Mounted, Two Gang, Brown



Blank Plates -- Box Mounted, Two Gang, Black



Blank Plates -- Box Mounted, Two Gang, Ivory



Blank Plates -- Box Mounted, Two Gang, Light Almond

- SPECIFICATIONS
- RESOURCES

features & benefits

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

Top 5 Resources

-  TradeMaster Thermoplastic Nylon Wall Plates, SF2501R1 (Cutsheet)

specifications

General Info

- Color: Gray
- Size: Standard
- Type: Box Mount
- Special Features: Unbreakable
- Style: Blank Plate

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121704
- U R: No

Dimensions

- Weight: 0.10437

Technical Information


- Material: Nylon
- Capacity: 2-gang

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
-



resources CUTSHEET

 [TradeMaster Thermoplastic Nylon Wall Plates, SF2501R1PDF \(353.88kb\)](#)