



designed to be better.

Search

Decorator Openings, Two Gang, Gray

TP262GRY

Trademaster Plate 2gang 2 Decorator Gray


Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Decorator Openings, Two Gang, White



Decorator Openings, Two Gang, Brown



Decorator Openings, Two Gang, Black



Decorator Openings, Two Gang, Blue



Decorator Openings, Two Gang, Ivory



Decorator Openings, Two Gang, Light Almond



Decorator Openings, Two Gang, Orange



Decorator Openings, Two Gang, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

Top 5 Resources

 TradeMaster Thermoplastic Nylon Wall Plates, SF2501R1 (Cutsheet)

specifications

General Info

- Color: Gray
- Size: Standard
- Special Features: Unbreakable
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121704
- U R: No

Dimensions

- Weight: 0.07514

Technical Information

- Material: Nylon
- Capacity: 2-gang

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
-



resources

CUTSHEET

 TradeMaster Thermoplastic Nylon Wall Plates, SF2501R1PDF (353.88kb)