









Decorator Devices Decorator Openings

Standard Size Plastic & Metal



Description	Color	Nylon	Thermoset	Metal	
		TradeMaster® Plates	Smooth	Material	Smooth
Decorator Openings					
One Gang 	Ivory White Brown Gray Black Red Light Almond Blue Orange	TP26I TP26W TP26 TP26GRY TP26BK TP26RED TP26LA TP26BL TP26OR	SP26I SP26W SP26 SP26GRY SP26BK SP26LA	Aluminum Brass Polished Brass 430S/S 302S/S Brushed Bronze Chrome	SA26 SB26 SB26PB SL26 SS26 SB26BZ SB26CH
Two Gang 	Ivory White Brown Gray Black Red Light Almond Blue Orange	TP262I TP262W TP262 TP262GRY TP262BK TP262RED TP262LA TP262BL TP262OR	SP262I SP262W SP262 SP262GRY SP262BK SP262LA	Aluminum Brass Polished Brass 430S/S 302S/S	SA262 SB262 SB262PB SL262 SS262
Three Gang 	Ivory White Brown Gray Black Red Light Almond	TP263I TP263W TP263 TP263GRY TP263BK TP263RED TP263LA	SP263I SP263W SP263GRY SP263BK SP263LA	Brass Polished Brass 302S/S	SB263 SB263PB SS263
Four Gang 	Ivory White Brown Gray Black Red Light Almond	TP264I TP264W TP264 TP264GRY TP264BK TP264RED TP264LA	SP264I SP264W SP264 SP264GRY SP264BK SP264LA	Brass Polished Brass 302S/S	SB264 SB264PB SS264
Five Gang 	Ivory White Brown Gray Black Red Light Almond	TP265I TP265W TP265 TP265GRY TP265BK TP265LA	SP265I SP265W SP265GRY SP265BK SP265RED SP265LA	302S/S	SS265
Six Gang 	Ivory White Brown Gray Black Light Almond	TP266I TP266W TP266 TP266GRY TP266BK TP266LA	SP266I SP266W SP266 SP266GRY SP266BK SP266LA	302S/S	SS266
Seven Gang 				302S/S 302S/S Painted Ivory 302S/S Painted White	SS267 SS267I SS267W
Eight Gang 				302S/S 302S/S Painted Ivory 302S/S Painted White	SS268 SS268I SS268W

These products listed to UL514, Cover Plates for Flush-Mounted Wiring Devices, CSA Certified.