

tZWRpYS9CMzdFODIEMzM2QjM0RjYyOEFDNkZFRkEwNUJENzUzQi5hc2h4IiBhbHQ9Ik1vZHVzZXMilHdpZHRoPSlyMTgilGhlaWdodD0iMTEyIiAvPjwv



designed to be better.

Search

Decorator Openings, Four Gang, Brown

TP264
Trademaster Plate 4gang 4 Decorator Brown
MSRP
\$11.07 USD

Submit Query

Where to buy

Submit Query

0



Representative image shown.

AVAILABLE OPTIONS



Decorator Openings, Four Gang, White



Decorator Openings, Four Gang, Black



Decorator Openings, Four Gang, Gray



Decorator Openings, Four Gang, Ivory



Decorator Openings, Four Gang, Red

- SPECIFICATIONS

features & benefits

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

specifications

General Info

- Color: Brown
- Size: Standard
- Special Features: Unbreakable
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cJ Lus: Yes
- cJ Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121704
- U R: No

Dimensions

- Weight: 0.13252

Technical Information

- Material: Nylon
- Capacity: 4-gang

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
-

