









Wall Plates

Single Receptacle & Power Outlet Openings

Standard Size Plastic & Metal



Description	Color	Nylon	Thermoset	Metal	
		TradeMaster® Plates	Smooth	Material	Smooth
Single Receptacle Openings					
One Gang 	Ivory White Brown Gray Black Red Light Almond	TP71 TP7W TP7 TP7GRY TP7BK TP7RED TP7LA	SP71 SP7W SP7 SP7GRY SP7LA	Aluminum Brass Polished Brass 430S/S 302S/S	SA7 SB7 SB7PB SL7 SS7
Two Gang 	Ivory White Brown		SP72I SP72W SP72	302S/S	SS72
Three Gang 				302S/S 302S/S Painted Ivory 302S/S Painted White 302S/S Painted Gray	SS73 SS73I SS73W SS73GRY
Power Outlet Receptacle Openings – One Gang					
 1.5938" hole for 1.5625" dia. device – 2 mtg. holes	Ivory White Brown Gray Light Almond	TP720I TP720W TP720 TP720GRY TP720LA	SP720I SP720W SP720 SP720GRY SP720LA	302S/S	SS720
 1.625" hole for 1.5938" dia. device – 2 mtg. holes				302S/S	SS721
 1.75" hole for 1.7186" dia. device-2 mtg. holes				302S/S	SS725
 2.125" hole for 2.094" dia. device – 2 mtg. holes				302S/S	SS723
 2.156" hole for 2.125" dia. device – 2 mtg. holes	Ivory White Brown Gray Black Light Almond	TP724I TP724W TP724 TP724GRY TP724BK TP724LA	384I 384	Chrome 302S/S	S384C SS724

These products listed to UL514, Cover Plates for Flush-Mounted Wiring Devices, CSA Certified.