









# Wall Plates

## Single Receptacle & Power Outlet Openings

Standard Size Plastic & Metal



Description	Color	Nylon	Thermoset	Metal	
		TradeMaster® Plates	Smooth	Material	Smooth
<b>Single Receptacle Openings</b>					
<b>One Gang</b> 	Ivory White Brown Gray Black Red Light Almond	TP71 TP7W TP7 TP7GRY TP7BK TP7RED TP7LA	SP71 SP7W SP7 SP7GRY  SP7LA	Aluminum Brass Polished Brass 430S/S 302S/S	SA7 SB7 SB7PB SL7 SS7
<b>Two Gang</b> 	Ivory White Brown		SP72I SP72W SP72	302S/S	SS72
<b>Three Gang</b> 				302S/S 302S/S Painted Ivory 302S/S Painted White 302S/S Painted Gray	SS73 SS73I SS73W SS73GRY
<b>Power Outlet Receptacle Openings – One Gang</b>					
 1.5938" hole for 1.5625" dia. device – 2 mtg. holes	Ivory White Brown Gray Light Almond	TP720I TP720W TP720 TP720GRY TP720LA	SP720I SP720W SP720 SP720GRY SP720LA	302S/S	SS720
 1.625" hole for 1.5938" dia. device – 2 mtg. holes				302S/S	SS721
 1.75" hole for 1.7186" dia. device-2 mtg. holes				302S/S	SS725
 2.125" hole for 2.094" dia. device – 2 mtg. holes				302S/S	SS723
 2.156" hole for 2.125" dia. device – 2 mtg. holes	Ivory White Brown Gray Black Light Almond	TP724I TP724W TP724 TP724GRY TP724BK TP724LA	384I  384	Chrome 302S/S	S384C SS724

These products listed to UL514, Cover Plates for Flush-Mounted Wiring Devices, CSA Certified.