



Pass & Seymour

Wall Plates TradeMaster® Thermoplastic Nylon One & Two Gang

TP1, TP2, TP8, TP82, TP26, TP262, TP13, TP23, TP7, TP720

Maximum durability in plastic wall plates.


Self-extinguishing nylon construction makes these TradeMaster® wall plates virtually unbreakable. They will not crack if excessive torque is applied to installation screws. They are 3/16" higher and wider than typical plastic wall plates — not enough to be apparent to the eye, but the extra size cuts costs by reducing dry wall rework.



Features & Benefits

An extra 3/16" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.

Molded of rugged, virtually unbreakable self-extinguishing .070 inch thick thermoplastic Nylon 6.



Aesthetically pleasing contour design.

TP26-W, TP2-I, TP8-LA

Pre-installed mounting screws on single gang toggle, duplex receptacle and decorator openings.







Field Uses/Vertical Markets





- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

SF2501R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour

Wall Plates TradeMaster[®] Thermoplastic Nylon One & Two Gang

Ordering Information

Description	Catalog Number	Color
TradeMaster Toggle Switch Openings		
One Gang 	TP1-I TP1-W TP1 TP1-GRY TP1-BK TP1-RED TP1-LA	Ivory White Brown Gray Black Red Light Almond
Two Gang 	TP2-I TP2-W TP2 TP2-GRY TP2-BK TP2-RED TP2-LA	Ivory White Brown Gray Black Red Light Almond
TradeMaster Duplex Receptacle Openings		
One Gang 	TP8-I TP8-W TP8 TP8-GRY TP8-BK TP8-RED TP8-LA TP8-BL TP8-OR	Ivory White Brown Gray Black Red Light Almond Blue Orange
Two Gang 	TP82-I TP82-W TP82 TP82-GRY TP82-BK TP82-RED TP82-LA TP82-OR	Ivory White Brown Gray Black Red Light Almond Orange
TradeMaster Decorator Openings		
One Gang 	TP26-I TP26-W TP26 TP26-GRY TP26-BK TP26-RED TP26-LA TP26-BL TP26-OR	Ivory White Brown Gray Black Red Light Almond Blue Orange
Two Gang 	TP262-I TP262-W TP262 TP262-GRY TP262-BK TP262-RED TP262-LA TP262-BL TP262-OR	Ivory White Brown Gray Black Red Light Almond Blue Orange

Description	Catalog Number	Color
TradeMaster Blank Plates — Box Mounted		
One Gang 	TP13-I TP13-W TP13 TP13-GRY TP13-BK TP13-RED TP13-LA	Ivory White Brown Gray Black Red Light Almond
Two Gang 	TP23-I TP23-W TP23 TP23-GRY TP23-BK TP23-LA	Ivory White Brown Gray Black Light Almond
TradeMaster Single Receptacle Openings		
One Gang 	TP7-I TP7-W TP7 TP7-GRY TP7-BK TP7-RED TP7-LA	Ivory White Brown Gray Black Red Light Almond
TradeMaster Power Outlet Receptacle Openings		
One Gang 	TP720-I TP720-W TP720 TP720-GRY TP720-LA	Ivory White Brown Gray Light Almond

For more information on these and other P&S products refer to our Product Guide or visit our web site.

TradeMaster® Thermoplastic Nylon One & Two Gang



Technical Specifications


3rd Party Compliance	
UL Listed, Standard UL514, Cover Plates for Flush Mounted Wiring Devices. CSA Certified.	

Performance	
Environmental	Chemical-Resistant
Flammability	UL94 V2


Materials	
Plate Material	.070" Nylon 6
Plate Finish	Matte
Screws	Steel, Heads Painted to Match Plate Color

Warranty

1 Year



Dimensions for TradeMaster One Gang




Dimensions for TradeMaster Two Gang

Complementary Devices & Accessories




WALL PLATES

- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers




WEATHERPROOF BOXES & COVERS

- While-In-Use Covers
- Heavy Cast Aluminum Covers
- Cast Covers
- Boxes



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF2501R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour