



designed to be better.

# Tamper-Resistant Commercial Grade Receptacles, Light Almond

TR20LA


Tamper-Resistant Commercial Grade Receptacles, 20A, 125V, Light Almond, TR20LA

Where to buy

Like

Tweet







## product gallery

Representative images shown.

### AVAILABLE OPTIONS



Tamper-Resistant Commercial Grade Receptacles, White



Tamper-Resistant Commercial Grade Receptacles, Brown



Tamper-Resistant Commercial Grade Receptacles, Black



Tamper-Resistant Commercial Grade Receptacles, Gray





Tamper-Resistant Commercial Grade Receptacles, Ivory

- SPECIFICATIONS

## features & benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.

## specifications

### General Info

- Color: light almond
- Type: Receptacles
- Features: Tamper-Resistant
- Number Of Poles: 2
- Number Of Wires: 3
- Special Features: Tamper-Resistant
- Style: Duplex

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- cU Lus: Yes
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406

### Dimensions

- Depth (U S): 1.130"
- Height U S: 3.281"
- Width U S: 1.322"

### Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: 5-20R
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Commercial

### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

