

XQtbGlnaHRpbmctcG93ZXIvdW5kZXItY2FiLWxpZ2h0aW5nLXN5c3RibS5hc3B4ZBYCZg8WAh8ABYIBPGItZyByZXBsYWNIPSJkc3JjliBkc3JjPSlvi9tZW



designed to be better.

Search

Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond

TR26362LA
Tamper-Resistant Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Light Almond

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0 0





product gallery

Representative images shown.

AVAILABLE OPTIONS



Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, White



Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Brown



Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Black



Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Gray



Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory



Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Red






- SPECIFICATIONS
- RESOURCES

features & benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive brass terminal screws for faster installation.
- Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for additional wiring flexibility.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- .032 inch thick brass triple-wipe power contacts.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

Top 5 Resources

-  [Tamper-Resistant Receptacles \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)
-  [Heavy Duty Decorator Tamper-Resistant Receptacles, SF907R1 \(Cutsheet\)](#)

specifications

General Info

- Color: light almond
- Type: Receptacles
- Duty: Heavy Duty
- Special Features: tamper-resistant,back,side wire

- Style: Decorator

Listing Agencies/Third Party Information

- CSA Standard: Yes
- cUL Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406

Dimensions

- Depth (U S): 0.833"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information


- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Federal Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources BROCHURE

-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

-  Heavy Duty Decorator Tamper-Resistant Receptacles, SF907R1PDF (310.72kb)