

8WAh8ABRFGaXJlc3RvcCBGaXR0aW5nc2QCAw8PFgJfBAUtL3dpcmUtY2FibGUtbWFuYWdlbWVudC9maXJlc3RvcC1maXR0aW5ncy5hc3B4ZBYCZg!



designed to be better.

Search

Tamper-Resistant Construction Spec Grade Single Receptacles, Back & Side Wire, 20A, 125V, Ivory

TR5351I

Tamper-Resistant Construction Spec Grade Single Receptacle Back & Side Wire 20amp 125volt Ivory

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0 0





product gallery

Representative images shown.

AVAILABLE OPTIONS



Tamper-Resistant Construction Spec Grade Single Receptacles, Back & Side Wire, 20A, 125V, White



Tamper-Resistant Construction Spec Grade Single Receptacles, Back & Side Wire, 20A, 125V, Brown



Tamper-Resistant Construction Spec Grade Single Receptacles, Back & Side Wire, 20A, 125V, Light Almond

- SPECIFICATIONS
- RESOURCES

features & benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.

Top 5 Resources

- [Tamper-Resistant Receptacles \(Brochure\)](#)
- [Commercial & Industrial Products \(Brochure\)](#)
- [Construction Grade Tamper-Resistant Single Receptacles, SF312R1 \(Cutsheet\)](#)

specifications

General Info

- Color: Ivory
- Type: Single, Receptacles
- Number Of Poles: 2
- Number Of Wires: 3
- Special Features: tamper-resistant,back,side wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 1.19"
- Height U S: 3.28"
- Width U S: 1.296"

Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: 5-20R
- Volts: 125V
- Volts A C: 125
- Capacity: Single
- Grade Type: Construction

Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

-  Construction Grade Tamper-Resistant Single Receptacles, SF312R1PDF (227.57kb)