

U2hIZXQgU0YzMTSRMSddKTsWBGYPDxYCHwgFly9pbWFnZXMvcHJvZHVjdC1kZXRhaWwvcGRmLWljb24uanBnZGQCAQ8WAh8ABUpIYXJkIFVzZS



designed to be better.

Search

Tamper-Resistant Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Ivory

TR5362I
Tamper-Resistant Hard Use Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Ivory

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0 0





product gallery

Representative images shown.

AVAILABLE OPTIONS



Tamper-Resistant Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, White



Tamper-Resistant Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Brown



Tamper-Resistant Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Black



Tamper-Resistant Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Gray



Tamper-Resistant Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Light Almond



Tamper-Resistant Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive brass terminal screws for faster installation.
- Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for additional wiring flexibility.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- .032 inch thick brass triple-wipe power contacts.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

Top 5 Resources

- [Tamper-Resistant Receptacles \(Brochure\)](#)
- [Commercial & Industrial Products \(Brochure\)](#)
- [Hard Use Tamper-Resistant Receptacles, SF314R1 \(Cutsheet\)](#)

specifications

General Info

- Color: Ivory
- Type: Receptacles
- Special Features: Back, Side Wire, Tamper-Resistant

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 1.130"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information



- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Specification

Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

-  Hard Use Tamper-Resistant Receptacles, SF314R1PDF (202.19kb)