



designed to be better.

Tamper-Resistant Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Black

TR63BK

Tamper-Resistant Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Black

Where to buy

Like

Tweet





•



•



•



•



product gallery

Representative images shown.

AVAILABLE OPTIONS



Tamper-Resistant Spec Grade Receptacles, Back & Side Wire, 20A, 125V, White



Tamper-Resistant Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Brown



Tamper-Resistant Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Gray



Tamper-Resistant Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory





Tamper-Resistant Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond





Tamper-Resistant Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.

Top 5 Resources

-  [Commercial & Industrial Products \(Brochure\)](#)
-  [Extra Heavy Duty Tamper-Resistant Receptacles, SF309R2 \(Cutsheet\)](#)

specifications

General Info

- Color: black
- Type: Receptacles
- Special Features: Tamper-Resistant,back, side wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 0.9"
- Height U S: 3.281"
- Width U S: 1.625"

Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

 [Extra Heavy Duty Tamper-Resistant Receptacles, SF309R2PDF \(336.02kb\)](#)