

9yZS1gaHJIZj0iL2VsZWN0cmJjYWwtd2lyaW5nLWRldmJjZXMvZWxiY3RyaWNhbC1zd2l0Y2hlcY5hc3B4Ij5WaWV3IEVsZWN0cmJjYWwgU3dpdGNoZXM8



designed to be better.  
Search

# Tamper-Resistant Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Red

TR63HRED  
Tamper-Resistant Hospital Grade Duplex Receptacle Back & Side Wire 20amp 125volt Red

Submit Query  
Where to buy Enter Postal Code Submit Query

Like 0 Tweet 0 0 Email Print



- 
- 
- 
-



## product gallery

Representative images shown.

### AVAILABLE OPTIONS



- SPECIFICATIONS
- RESOURCES

### features & benefits

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground.
- One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground.

### Top 5 Resources

- [Tamper-Resistant Receptacles \(Brochure\)](#)
- [Commercial & Industrial Products \(Brochure\)](#)
- [Hospital Grade Tamper-Resistant Receptacles, SF704R1 \(Cutsheet\)](#)

### specifications

#### General Info

- Color: red
- Type: Receptacles
- Special Features: Tamper-Resistant,back, side wire

#### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

#### Dimensions

- Depth (U S): 0.9"
- Height U S: 3.281"
- Width U S: 1.625"

#### Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Hospital

#### Buy American Act Compliance

- Country of Origin: MEXICO


- Buy American Act Status: Trade Agreement Act Compliant



**resources**  
**BROCHURE**

-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)

**CUTSHEET**

-  Hospital Grade Tamper-Resistant Receptacles, SF704R1PDF (146.08kb)