



Accessories

Product	Description/Specifications
<p>ZHRMU*</p> 	<p>Remote Monitoring Unit – Offers clear audio/visual indication of the status of the surge suppressor unit. Can be installed remotely or adjacent to the suppressor. Powered locally by a plug-in transformer (included). Can also be used as a stand-alone diagnostic device using NO/NC dry contacts.</p> <p>SPECIFICATIONS</p> <p>Dimensions: 5 1/8" x 4" x 1 1/2" [135mm x 102mm x 38mm]</p> <p>Weight: 1 lb.</p> <p>Protection Indication: Bright green LED: Illuminated</p> <p>Fault Indication: Audible alarm. Bright red LED: Illuminated</p> <p>Test Functions: Switch tests audible alarm (checks monitoring circuitry)</p> <p>Silent Function: Switch silences audible alarm</p> <p>Connections: Accepts wires up to #14 AWG</p>
<p>ZHRMU250</p>	<p>Cable for Remote Monitoring Unit – 250' [76.2m] cable for use with ZHRMU Remote Monitoring Unit is available or use your own cable to connect the device.</p>
<p>PABFMC</p>	<p>Flush Mount Cover – For installing PA/PB units on sheetrock or firewall construction. Cover hides the hole cut and gives the unit a finished look. Brushed metal cover can be painted to match any decor.</p> <p>SPECIFICATIONS</p> <p>Dimensions: 9" x 7" [229mm x 178mm]</p>

* **NOTE:** ZHRMU can only be used on PA/PB Units with remote contacts (Option A). ZHRMU is also compatible with all ZoneMaster Units (see ED1165 for details).



PA and PB Series Panel Protection Devices



The Sentrex PA and PB Series surge protection devices protect your sensitive electronic equipment from external or internal transient activity. Units can be customized with remote monitoring, noise filtration and flush mount options.


All PA and PB units are approved for indoor or outdoor use and feature all-mode protection. Units provide excellent protection when placed at branch panels or at specific pieces of equipment. They can also suppress external surges when mounted at the main service panel.

PA and PB Series surge protection devices are an integral part of the Sentrex Zoned Approach to Whole Building Protection.



The PA and PB Series provide surge protection at the main service panel, sub panel or at sensitive equipment.

Features & Benefits

- Up to 160kA maximum surge current protection per phase.
- **Easy installation.** Enclosure can be easily drilled or punched for conduit/cable access and positioned to the electrical panel at the discretion of the installer.
- **All-mode protection is standard on all units.**
- **NEMA 1, 2, 3, 3S, 4, 4X, 12, 13 rated, water-tight, fire-resistant plastic enclosure.**
- **34mm MOV circuitry.** Well exceeds the capacity of 20mm MOVs in parallel to manage surges over time.
- Short circuit and thermal fusing.
- Low impedance circuitry.
- Visual indication of protection status.
- Ten-year product warranty.
- UL1449 Second Edition Listed.
- 

Available Options

- **Remote diagnostic connection.** Using NO/NC dry contacts via on-board relay. Remote monitoring device sold separately.
- **EMI/RFI noise filter.** Noise attenuation -20dB maximum 100 kHz to 100 MHz.
- **Flush mount cover.** Sold separately.