



## SURGE PROTECTED DUPLEX POWER KIT

364569-02-V1 | [On-Q](#)

### FEATURES & BENEFITS

This surge protected outlet kit is the power source of devices mounted in the low voltage enclosure. It is designed to mount in the rectangular knockout location at the bottom of the enclosure.

Surge suppression provides protection for hot to neutral, hot to ground, and neutral to ground. The audible alarm signals when surge protection has expired.

- 120VAC, 15A
- Connect with the AC1031 to add six AC power outlets in the enclosure
- Kit includes a surge protected duplex outlet, metal junction box, and a faceplate kit

### SPECIFICATIONS

#### GENERAL INFO

Color: White

Termination:

Brass	HOT
Nickel	NEUTRAL
Green	GROUND

Type: Surge-Suppressing Outlet

Input Plug Type: NEMA 5-15R Male

Number Of Poles: 2

Number Of Wires: 3

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Screws

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 39121610

#### CONSTRUCTION INFORMATION

Installation Location: On-Q enclosures

## DIMENSIONS

Depth (Metric): 4.8 cm  
Depth (US): 1.9"  
Height (Metric): 11.4 cm  
Height (US): 4.5"  
Width (Metric): 7 cm  
Width (US): 2.75 in

## TECHNICAL INFORMATION

AC Voltage Output: 120 VAC  
Amps: 15A  
Connection Method: Screw terminal  
Frequency: 60 Hz  
Material: Thermoplastic  
Max Surge Current: 9kA  
Mounting: Enclosure base  
Noise Reduction: 7:1  
Operating Temperature (Celsius): -20°C to 55°C  
Product Fits Into: Single-Gang  
Storage Temperature: -40°C to 85°C  
Wire Gauge: 10 - 14 AWG, copper conductor only  
Receptacle Type: NEMA 5-15R Female  
Number Of Receptacles: 2  
Surge Suppression: UL1449 Transient Voltage Surge Suppressor