



300W PLUG-IN LAMP MODULE, WHITE

MRP6-W | [On-Q](#)

FEATURES & BENEFITS

USAGE

Perfect for control table and floor lamps up to 300 W with this plug-in module.

GETTING STARTED

- Time to install: 25 minutes or less.
- Plugs into any grounded, 120V outlet.
- Auto-ON feature ensures load receives power if occupant turns switch ON manually
- This item requires the adorne Hub. [Shop now](#) to learn how Wi-Fi ready lighting solutions can transform your home.

SPECIFICATIONS

GENERAL INFO

Color: White

Connection Type: NEMA 5-15R Male

Type: Plug-In Lamp Module

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: CAN/CSA-C22.2 No. 14- 2005

CSA Standard: Yes

FCC Standard: Yes

UL Listing No: UL 244A

UL Standard: Yes

UN SPSC: 39122206

DIMENSIONS

Depth (Metric): 4.13 cm

Depth (US): 1.625"

Height (Metric): 8.9 cm

Height (US): 3.5"

Width (Metric): 5.7 cm

Width (US): 2.25 in

TECHNICAL INFORMATION

Frequency: 900 MHz

Humidity: 0-80% relative humidity, noncondensing

Material: High Impact Plastic

Mounting: NEMA 5-15R Outlet

Operating Temperature (Celsius): 0°C to 40°C

Reset: Press and hold up and down buttons

Supported Standards: Topdog™ RF communication protocol

Volts (AC): 120 VAC

Watts: 25W - 300W Loads Supported