



NON-NEMA 3 WIRE DUPLEX RECEPTACLE, GROUNDING

7580G | [Pass & Seymour](#)

FEATURES & BENEFITS

Receptacle Duplex 15amp 125volt 10amp 250volt Turnlok



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

SPECIFICATIONS

GENERAL INFO

Type: Duplex, Receptacles
Number Of Wires: 3
Special Features: Non-NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.199"
Height (US): 2.635"
Width (US): 1.500"

TECHNICAL INFORMATION

Amps: 15A
Volts: 250V
Volts (AC): 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

