



IN-WALL SWITCH, WHITE

DRD3-W V2 | [On-Q](#)

FEATURES & BENEFITS

The DRD3 switch can easily control any non-dimmable load or device. As part of the RF Lighting Control System, it can be controlled from other devices located anywhere in the home.

- Patented Top Dog™ RF communication protocol; 900MHz radio. Avoids interference with other 900MHz devices, such as cordless phones and baby monitors.
- Patented overload and short circuit protection.
- No control wiring necessary.
- Large surface-mounted antenna ensures maximum broadcast coverage.
- Stores room and house scenes.
- Compatible with Decorator wall plates.
- 5-year warranty.
- **Note:** Wall plate sold separately from device.

SPECIFICATIONS

GENERAL INFO

Color: White

Connection Type: Screw Terminals

Type: RF Switch

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: CAN/CSA-C22.2 No. 14- 2005

CSA Standard: Yes

cUL Standard: Yes

FCC Standard: Yes

UL Listing No: UL 244A

UL Standard: Yes

UN SPSC: 39122226

DIMENSIONS

Depth (Metric): 4.8 cm

Depth (US): 1.88"

Height (Metric): 10.8 cm

Height (US): 4.25"
Width (Metric): 4.3 cm
Width (US): 1.69"

TECHNICAL INFORMATION

Frequency: 900 MHz
Humidity: 0-80% relative humidity, noncondensing
Material: High Impact Plastic
Mounting: Electrical Box
Operating Temperature (Celsius): 0°C to 40°C
Reset: Press and hold up and down buttons
Supported Standards: Topdog™ RF communication protocol
Volts (AC): 120/277 VAC
Watts: 1500 W (120V), 3000W (277V)