
OUTDOOR MOTION SENSORS

EW-200 Series | [Wattstopper](#)



FEATURES & BENEFITS

Wattstopper's EW line voltage outdoor motion sensors provide occupancy based control of outdoor lighting. Raintight and rated for -40°F to 130°F, EW sensors perform reliably in all weather conditions.

- 120 VAC or 277 VAC operation
- Optional model with lampholders
- Rated for use in temperature range of -40° to 130°F
- Weatherproof and raintight for reliable performance
- Isolated relay enables interface with security systems or other loads
- Adjustable light level and time delay settings
- 270 or 180 degree field of view

SPECIFICATIONS

MODELS

Product Number: EW-200-120-W, EW-200-120-G, EW-200-277-W, EWF-205-120-W

GENERAL INFO

Typical Applications: Walkways, Parking Lots, Dock Lighting, Warehouses, Garages, Backyards, Entranceways
Special Features: UL 773A rated raintight

TECHNICAL INFORMATION

Load: 1 Amp@ 30VDC/VAC
Volts: 120/277VAC