



## SELECTIVE CALL INTERCOM VIDEO DOOR UNIT, OIL-RUBBED BRONZE

IC5003-OB | [On-Q](#)

### FEATURES & BENEFITS

This innovative door unit, housed in an attractive weatherproof finish, includes a wide-angle color camera for front door monitoring. When integrated with the On-Q camera system LCD, the doorbell press enables the image from the door unit camera to appear on the LCD screen. The image can also appear on any TV connected to a TV display port.

- Crisp color image also performs well in low-light conditions.
- Includes up to 20 digital door tones.
- As part of the Studio collection this innovative video door unit enhances the curb appeal of any home.
- Installs in a standard double gang opening with simple RJ45 plug design for easy installation and troubleshooting.

### SPECIFICATIONS

#### GENERAL INFO

Color: Oil Rubbed Bronze

#### CONSTRUCTION INFORMATION

Spec 1: Power Requirements

#### DIMENSIONS

Overall Dimensions (US): 5.1" H x 4.5" W x 1.8" D

Product Weight (US): 1.5 lbs

Weight: 1.5 lb

#### CORD INFORMATION

Pinning:

Pin 1 24 VDC Out

Pin 2 GND

Pin 3 Audio (+)

Pin 4 COMM A

Pin 5 COMM B

Pin 6 Audio (-)

Pin 7 VIDEO  
INPUT  
Pin 8 GND

#### TECHNICAL INFORMATION

Cat5 Cable Rating: CAT5 UTP, 4 pair solid conductor (24 AWG)

Firmware Update: 16 Pin Header Connector

Humidity: Up to 90% RH (non-condensing)

Material: Cast; Zinc Alloy

Operating Temperature (Celsius): -25 to 55 degrees

Power Requirements: +24Vdc, +/-1.5Vdc, 0.15A max

QLink Selective Call Ports: RJ-45

Storage Temperature: -45 to 85°C (-49 to 185°F)

Viewing Angle: Horizontal: 105 degrees; Vertical: 80 degrees