
4-ROOM WHOLE HOUSE MUSIC & INTERCOM, OIL-RUBBED BRONZE

ICAU14-OB | [On-Q](#)



FEATURES & BENEFITS

The perfect all-in-one solution for whole-home audio and intercom. Easily add additional room stations and up to three patio stations for a total of 12 intercom stations.

Kit Includes:

- 1 **AU7396** Single Source 4 Zone Distribution Module
- 1 **AU1004-WH** Flush Mount Single Source Input
- 4 **AU7394-WH** IyriQ Classic Standard Performance Keypad Volume Control
- 4 **MS3652** 3000 Series 6.5inch In-Ceiling Dual Voice Coil Speakers
- 1 **IC1000** Broadcast Intercom Main Module
- 4 **IC1004-WH** Broadcast Intercom Room Stations
- 1 **F7601** Broadcast Intercom Door Chime Module
- 1 **IC1001** Audio Interrupt Module
- 1 **F7596-OB** Broadcast Intercom Door Station
- 1 **PW1060** 24v, 2.5 Amp Power Supply
- 1 **PW7725** 12v, 2.5Amp Power Supply
- 1 **WP1205-WH** Single Gang Decorator Wall Plate
- 1 **F7425** Dual Head IR Emitter
- 1 **AU1060** IyriQ Dual Head IR Emitter

SPECIFICATIONS

GENERAL INFO

Cable Type: Cat 5, Speaker Cable
Color: Oil Rubbed Bronze
Connection Type: RJ45, 110 Punchdown, Terminal Block
Type: Intercom/Audio Kit

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 45111801

TECHNICAL INFORMATION

Compatible Power Supplies: 24V 60W PW1060 (included), 12V 30W PW7725 (included)

Drywall Hole Size: Speaker: 7.75 in (diameter)
Efficiency: Speaker: 91dB
External Power Input: Power over Ethernet
Frequency Response: Speaker: 60Hz - 20KHz
Mounting: Enclosure, Ceiling, Electrical Box
Power Peak: Speaker: 100W
Power RMS: Speaker: 50W
Speaker Depth (Metric): 93.1 mm
SpeakerDepth (US): 3.665 in
Speaker Impedance Load: 6 ± 0.9 ohms
Tweeter Type: PEI Mylar
Woofer Type: Mica Fiber