



300W PLUG-IN LAMP MODULE, WHITE

MRP6-W | [On-Q](#)

FEATURES & BENEFITS

Control table and floor lamps up to 300 W with this plug-in module.

- Plugs into any grounded, 120V outlet
- Auto-ON feature ensures load receives power if occupant turns switch ON manually

SPECIFICATIONS

GENERAL INFO

Color: White
Connection Type: NEMA 5-15R Male
Type: Plug-In Lamp Module

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: CAN/CSA-C22.2 No. 14- 2005
CSA Standard: Yes
FCC Standard: Yes
UL Listing No: UL 244A
UL Standard: Yes
UN SPSC: 39122206

DIMENSIONS

Depth (Metric): 4.13 cm
Depth (US): 1.625"
Height (Metric): 8.9 cm
Height (US): 3.5"
Width (Metric): 5.7 cm
Width (US): 2.25 in

TECHNICAL INFORMATION

Frequency: 900 MHz
Humidity: 0-80% relative humidity, noncondensing
Material: High Impact Plastic
Mounting: NEMA 5-15R Outlet

Operating Temperature (Celsius): 0°C to 40°C

Reset: Press and hold up and down buttons

Supported Standards: Topdog™ RF communication protocol

Volts (AC): 120 VAC

Watts: 25W - 300W Loads Supported