



1-GANG, 4-PORT OVERSIZED WALL PLATE, LIGHT ALMOND

WP3304-LA | [On-Q](#)

FEATURES & BENEFITS

Our durable Oversized Wall Plates are available in White and Light Almond and come in your choice of blank, 1, 2, 3, 4, or 6 openings.



SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Product Series: Classic
Type: Oversized Keystone Wallplate

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: CAN/CSA-C22.2 No. 182.4-1990
CSA Standard: Yes
UL Listing No: ANSI/UL 1863
UL Standard: Yes
UN SPSC: 39121704

CONSTRUCTION INFORMATION

Installation Location: In-Wall

DIMENSIONS

Depth (Metric): 6 mm
Depth (US): 0.22"
Height (Metric): 12.4 cm
Height (US): 4.87"

Width (Metric): 7.9 cm

Width (US): 3.11 in

TECHNICAL INFORMATION

Material: High Impact Flame Retardant Plastic

Receptacle Type: Keystone Cutout

Number Of Receptacles: 4