



CAT 6 RJ45 KEYSTONE CONNECTOR

WP3460-GY | [On-Q](#)

FEATURES & BENEFITS

This high quality insert is for use in all Keystone Wall Plates



- Creates an Ethernet port
- Connects to Cat5, Cat5e, or Cat6 cables terminated with RJ-45 plugs Rear retention caps ensure secure wire termination
- Vertical design for easy punchdown termination
- T658A and T568B wiring labels included
- Meets Category 6 described in TIA/EIA-568-B.2
- Insertion and extraction life is 750 Cycles Min
- Jack housing is high-impact, flame resistant plastic, UL 94V-0
- Spring wire is phosphor bronze alloy plated with 50 micro-inch of gold over 100 micro-inches of nickel

SPECIFICATIONS

GENERAL INFO

Color: Gray
Mod Jack Wiring: T568A or T568B
Number Of Ports: 1
Pair Count: 4
Termination: IDC Wire Guage: 22-24 AWG

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
UL Listing No: ANSI/UL 1863; CAN/CSA-C22.2 No. 182.4-1990

DIMENSIONS

Height (US): 0.87"
Length (US): 1.28"
Width (US): 0.64"
Product Weight (US): 0.0255 lb

TECHNICAL INFORMATION

Humidity: Max 93% non-condensing
Material: High Impact Plastic
Mounting: Keystone
Storage Temperature: Neg 40°F to 158°F