



## WEATHER-RESISTANT COMMERCIAL GRADE RECEPTACLES, LIGHT ALMOND

WR20TRLA | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Weather-Resistant Commercial Grade Receptacles, 20 amp, 125 volts, Light Almond, WR20TRLA

- Auto-ground clip assures positive ground.
- WR marking on face as required by UL Standard.
- Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Tri-drive brass terminal screws. Internal screwpressure plate back and side wire capability. Two back wire holes for more wiring flexibility.
- Heavy-duty, brass strap for added strength and ground conductivity.
- UV-resistant nylon face for longer life under adverse environmental conditions.
- Two drive screws anchor strap to backbody and face where abrupt removal torque is strongest.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond

Type: Receptacles

Features: Weather-Resistant

Number Of Poles: 2

Number Of Wires: 3

Special Features: Weather-Resistant, Tamper-Resistant

Style: Duplex

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

## **DIMENSIONS**

Depth (US): 1.130"

Height (US): 3.281"

Width (US): 1.322"

## **TECHNICAL INFORMATION**

Amps: 20A

NEMA Configuration Number: 5-20R

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

## **BUY AMERICAN ACT COMPLIANCE**

Buy American Act Status: Trade Agreement Act Compliant