

6020-C0W

Cheetah™

Item Description

Cheetah 4-Way Toggle Switch. 15A, 120VAC, No Ground. Residential Grade. Side & Quickwire. Non-Metallic strap for use with Cheetah Wallplates Only. White.



Technical Information

Electrical Specifications

Dielectric Voltage: Withstands 1500V minimum

Overload: Minimum 4.8 times rated current for 100 cycles

Current Interrupting: Certified for current interrupting at full rated current

Temperature Rise: Max 30°C temp rise at full-rated current after 50 cycles of OL at 150% rated current

Endurance: 50,000 cycles minimum, resistive, inductive, tungsten filament lamp load (Fed Spec.)

Environmental Specifications

Flammability: UL94V-2

Operating Temperature: -40C to 60C

Mechanical Specifications

Terminal ID: UL20 - Brass (hot), Black (hot)

Terminal Size: #14 -#10 AWG Copper Conductor Only

Product ID: Ratings are permanently marked on device

Standards and Certifications

NEMA: WD-1 & WD-6

ANSI: C-73

UL: 20

CSA C22.2: No. 111

UPC Code: 07847747041

Country of Origin: China

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

