


True Touch™ Decora Touch Dimmers



Cat. No. TT110-10



True Touch

APPLICATION

The new True Touch™ Decora Digital Touch Dimmer is ideal for applications where a low-profile contemporary touch dimmer is desired. True Touch provides fingertip full-range dimming control for incandescent and magnetic low-voltage lighting. Touch once anywhere on the pad to turn lights ON at preset level; touch once anywhere for OFF. Touch and hold to select the precise brightness level desired. True Touch provides full-range single-pole and multi-location dimming when used with remote unit.

FEATURES

- UL Listed (File # E-31373)
- CSA Certified (File # LR-3413)
- True Touch provides fingertip ease of use and precise adjustment of lighting levels. Simple one-touch for ON at preset level or OFF; touch and hold for BRIGHT/DIM lighting control.
- True Touch dimmers feature a locator LED that illuminates when the lighting load is OFF. (Remote units do not have locator LED)
- Protected memory during temporary power failures ensures that True Touch will retain last setting before power interruption.
- Provides single-pole dimming and 3-way multi-location dimming when used with Remote Dimmer (Cat. No. TT00R-1).
- Cat. No. 6606 Decora Touch Dimmer available for single-pole applications only. (No soft-ON/Fade-OFF or multi-location features).
- Digital circuitry provides Soft-ON/Fade-OFF switching for an eye-pleasing effect and extended lamp life.
- Built-in radio/TV interference filter.
- Use with Leviton Power Extender to extend load capacity.
- Attractive Decora styling blends with any interior.
- Compatible with Decora screwless and Decora standard designer wallplates
- Available in ivory, white, almond, white-silver and ivory-gold. Color change kits available in many additional color combinations

LEVITON SPECIFICATIONS SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Product Specifications

True Touch

STANDARDS SPECIFICATIONS

Controls shall be UL Listed Leviton Multi-Location digital, full-range Touch Dimmer with Limited Two-Year Warranty, low-profile contemporary design, and fingertip full-range dimming control for incandescent and magnetic low-voltage loads. Device shall feature a locator LED that illuminates when lighting is OFF, protected memory during temporary power failures and single-pole and 3-way dimming when used with Remote Dimmer (Cat. No. TT00R). Available in ratings and colors as scheduled on plan.

Performance Specifications	
Electrical	<ul style="list-style-type: none"> • Input 120 VAC @ 60Hz. • 600W, 1000W and 1000VA power rating; 2000W with use of power extender. • Line Voltage Regulation. • Incandescent and magnetic low voltage applications. • Mult-gang operation. • Remote control.
Mechanical	<ul style="list-style-type: none"> • Dimmer control – touch panel. • Push on/off switch control. • Three wire device with ground wire. • The LED will be lighted when the device switches the load off. • Air-gap switch for servicing provided.
Environmental	<ul style="list-style-type: none"> • Operating 0 degrees celsius to 55 degrees celsius. • Non-operating –10 degrees celsius to 85 degrees celsius. • Relative humidity, non-condensing 20% to 90%.

ORDERING INFORMATION

Cat. No.	Rating	Description
6606	600W	Incandescent, Single-Pole Only I, W, AA, AI, AW, AGY, AE
TTI06-10	600W	Incandescent
TTI10-10	1000W	Incandescent
TTM10-10	1000VA (750W)	For Magnetic Low-Voltage Lighting
TT00R-10	Remote	Multi-Location Dimming Remote
TTKIT	Dimmer Color Change Kit	I, W, A, WS, GI, GY, E, BG
TTKTR	Remote Color Change Kit	I, W, A, WS, GI, GY, E, BG

Cat. No. 6606 available in Brown/Gold (no dash), Ivory/Gold (-I), White/Silver (-W), Almond (-AA), Ivory (-AI), White (-AW), Gray (-AGY), and Black (-AE). Cat. Nos. TTI06, TTI10, TTM10 and TT00R are available in Ivory (-I), White (-W) and Almond (-A). Color Change Kits are available for these devices as follows: Ivory (-I), White (-W), Almond (-A), Gray (-GY), Black (-E), White frame/Silver touch plate (-WS), Ivory frame/Gold touch plate (-GI) and Brown frame/Gold touch plate (-BG).

Leviton's Limited Two- Year Warranty

This warranty gives you specific rights, and you may also have other rights, which vary in different states and countries. Leviton warrants to the original consumer purchaser that this product is free of defects in materials and workmanship for 2 years from the purchase date. Leviton's only obligation is to correct such defects by repair or replacement, at its option, if within such 2 years the product is returned prepaid, with proof of purchase date, and a description of the problem to the Leviton Manufacturing Co., Inc., ATTN: Quality Assurance Department, 59-25 Little Neck Pkwy., Little Neck, NY 11362-2591. This warranty does not cover labor for removal or reinstallation of the product and is void on any product installed improperly or in an improper environment, overloaded, misused, opened, abused, or altered in any manner. There are no implied warranties of any kind, but if implied warranties are required by the applicable jurisdiction, Leviton limits the duration of any implied warranty of fitness for use or merchantability to 2 years. Leviton is not liable for incidental or consequential damages, including without limitation, loss of equipment use and lost sales or profits for breach of any warranty on this product. Some jurisdictions may not allow exclusion of or limitations on how long an implied warranty lasts or the exclusion or limitation of incidental or consequential damages, so the above exclusions or limitations may not even apply to you.

LEVITON SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>
JOB NUMBER: <input type="text"/>	<input type="text"/>