



Actual

Catalog Number: 10-405
Product ID: 7TAA008610R0001
UPC Number: 78378600474
EAN Number: 05415022189605
Status: Active

High temperature Porcelain Wire Connector HI-5.

- Three sizes accommodate #18-14AWG stranded Copper
- 300 Volt rated.
- For high temperature applications over 105 degree C

North American Specifications (UNSPSC)

UNSPSC	39121445 Twist on wire connector
IGCC	4665 Twist on wire connector
Brand Name	T&B
Type	Wire Connectors & Termination
Special Features	Three sizes accommodate #18-14AWG stranded Copper
Application	For high temperature applications over 105 degree C
Standard	UL E9809, CSA 6591
Conductor Range	#18- 14 AWG
Material	Porcelain
Color	White
Voltage Rating	300V
Temperature Rating	Over 105 Degrees Celsius (221 F)

Packaging

Outer Quantity	100
Outer Dimensions (inches)	5.3x3x2.1
Weight Uom	3.75 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com