

T5630-T



UPC Code: 07847761063

Country of Origin: China

Combination Devices

Brand Features

Leviton's USB Charger/Tamper-Resistant Receptacle offers a ground-breaking 2.1A of charging power and a 15A-125V Tamper-Resistant Receptacle. This state-of-the-art device has the ability to charge up to two electronic devices simultaneously utilizing the USB Ports, leaving the receptacle free for additional power needs. The USB Ports are Type A, 2.0/3.0 and are controlled by a smart chip which recognizes and optimizes the charging power of your device. This means you can spend less time charging your device and more time enjoying it! Leviton's USB Charger/Tamper-Resistant Receptacle is ideal for charging tablets, smart and mobile phones, e-readers and much more.

Item Description

Combination Receptacle and USB Charger. 15 Amp, 125 Volt, Decora Tamper-Resistant Receptacle, NEMA 5-15R. 2.1 Amp, 5VDC, 2.0/3.0 Type A USB Chargers. Grounding, Side Wired & Back Wired - Light Almond.

Technical Information

Electrical Specifications

Receptacle Amperage: 15 Amp

Receptacle Voltage: 125V AC

Input Voltage Range: 108-305 Volt

Horsepower Rating: 15A-1/2 HP; 20A-1 HP

Ratings: 15A-125V

Grounding: Grounding

Environmental Specifications

Operating Temperature: -10C to 60C

Flammability: Rated V-2 per UL94

Material Specifications

Cover Material: Thermoplastic

Strap Material: Steel

Color: Light Almond

Body Material: Thermoplastic

Mechanical Specifications

Torque Range: 12-14 inch pounds

Terminal Accom.: 14-12 AWG

Product ID: Stamped on Strap

Termination: Back & Side

Terminal ID: Brass-Hot Black-Hot White-Neutral Green-Gnd

Standards and Certifications

Warranty: 5 Year Limited

cULus: Listed

NOM: 057

FCC Part 15: Class B for Residential Compliance

Features and Benefits

- The USB Receptacle is perfect for residential applications such as kitchens, bedrooms and home offices; and for light commercial applications such as hotels, airport cafes, restaurants, office cubicles and college dorm rooms.
- Key Features:
 - Smart chip designed for recognizing and optimizing the charging requirements of your device
 - Strategic Placement of ports positioned vertically provides more space for maneuvering and reduces stress on USB cables
 - USB Ports with a combined power of 2.1A. More charging capacity means better charging capability
 - High Power Port is ideal for charging Tablets and other high draw devices
 - Compact Design fits in a standard wallbox, is compatible with standard wallplates and can be multi-ganged with other standard Leviton devices

- Back and Side Wired for easy installation
- Tamper-Resistant 2011 NEC® Compliant shutter mechanism blocks access to contacts from most foreign objects for improved safety
- UL Listed

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012-2013 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

