

8200-T



Color: Light Almond

8200-T

Brand Features

All Leviton Hospital Grade Receptacles undergo the most stringent UL testing to assure continuous, safe operation in any application requiring high-abuse tolerance, including health care facilities, manufacturing plants and schools.

Item Description

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Extra Heavy Duty Hospital Grade, Duplex Receptacle, Straight Blade, Self Grounding, Back & Side Wired, 8 Hole Feed-Thru - LIGHT ALMOND

Where To Buy

Market Channel

enter your zip code



[Technical Information](#) [Support](#) [Related Products](#)

UPC Code: 07847747520
Country Of Origin: Please Contact Customer Service.

NEMA:
5-15R



Choose a Color



Product Lists

[Add to Product List](#)

[View Product List](#)

Quantity:

Technical Information

TOP

AC Horsepower Ratings

Horsepower Rating: 1/2 HP

Electrical Specifications

Amperage: 15 Amp
Current Limiting: Full Rated Current
Dielectric Voltage: Withstands 2000V per UL498
Grounding: Self-Grounding
Pole: 2
Temperature Rise: Max 30C after 250 cycles OL at 200 percent rated current
Voltage: 125 Volt
Wire: 3

Environmental Specifications

Flammability: Rated V-2 per UL94
Operating Temperature: -40C to 60C

Material Specifications

Body Material: Nylon
Clamp Nuts: Zinc-Plated Steel
Color: Light Almond
Face Material: Nylon
Ground Clips: Nickel-Plated Brass
Grounding Screw: Plated Brass
Line Contacts: Nickel-Plated Brass Triple-Wipe .040 Thick
Strap Material: Nickel-Plated Brass
Terminal Screws: Nickel-Plated Brass 10-32

Mechanical Specifications

Product ID: Markings are permanently marked on device
Terminal Accom.: 14-10 AWG
Terminal ID: Brass-Hot, Green-Ground, Silver-Neutral
Torque Range: 14-16 inch pounds

Product Features

Color: Light Almond
Grade: Hospital
NEMA: 5-15R

Standards and Certifications

ANSI: C-73
CSA C22.2 No. 42: File 152105
NEMA: WD-6
NOM: 057
RoHS: Non-Compliant
UL498HG: File E13399
UL Fed Spec WC-596: File E13399
Warranty: 10-Year Limited

[Dimensional Data](#)

[Instruction Sheet](#)

[Wiring Diagram](#)

Related Products



8200

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Extra Heavy Duty Hospital Grade, Duplex Receptacle, Straight Bla...
[More](#)



8200-GY

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Extra Heavy Duty Hospital Grade, Duplex Receptacle, Straight Bla...
[More](#)



8200-I

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Extra Heavy Duty Hospital Grade, Duplex Receptacle, Straight Bla...
[More](#)

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Extra Heavy Duty Hospital Grade, Duplex Receptacle, Straight Bla...
[More](#)

ABOUT LEVITON

Leviton is the smart choice, delivering the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial customers in more than 90 countries across the globe. From simple switches and receptacles, to networking systems and smart home automation, Leviton exceeds market needs by delivering innovative products to create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, LED lighting and lighting energy management systems, and security and automation applications. For Leviton, it is clear the FUTURE IS ON.



PRODUCTS

- Connected Home
- Electric Vehicle Charging
- Electrical Wiring Devices
- GFCIs and AFCIs
- Lighting Controls
- Network Solutions
- Security & Automation
- Submetering
- Surge Protective Devices
- Temporary Power

SOLUTIONS

- Applications
- Brands
- Business
- Contech Lighting
- Intense Lighting
- Energy Management
- Government
- Home Solutions
- Industrial
- JCC Lighting Products
- Security & Automation

SUPPORT

- Contact Us
- Cross Reference
- Discussions
- Documents & Resources
- ez-Biz
- ez-Learn
- Knowledgebase
- Leviton Warranties
- Mobile Apps
- Product Support
- Quality Concerns