

T5832-HGI





Color: Ivory

UPC Code: 07847768558
Country Of Origin: China

NEMA:
5-20R



Choose a Color



T5832-HGI

Item Description

Hospital Grade Combination Duplex Receptacle and USB Charger. 20 Amp, 125 Volt, Decora Tamper-Resistant Receptacle, NEMA 5-15R. 3.6 Amps, 5VDC, 2.0 Type A USB Chargers. Grounding, Side Wired & Back Wired - IVORY

Where To Buy

Market Channel

enter your zip code

[Technical Information](#) [Support](#) [Related Products](#) [Videos](#)

Technical Information

[TOP](#)

AC Horsepower Ratings

At Rated Voltage: 1 HP

Electrical Specifications

Amperage: 20 Amp
Dielectric Voltage: Withstands 2000V per CSA

Grounding: Self-Grounding

Pole: 2

Temperature Rise: Max 30C after 100 cycles OL

Voltage: 125 Volt

Wire: 3

Environmental Specifications

Flammability: Rated V-0 per UL94

Operating Temperature: -10C to 40C

Material Specifications

Body Material: PBT Thermoplastic polyester resin

Face Material: PBT

Ground Clips: Brass

Grounding Screw: Steel

Line Contacts: Brass

Strap Material: Steel

Terminal Clamp: Brass

Terminal Screws: Steel

Mechanical Specifications

Product ID: Stamped on Strap

Terminal Accom.: 14-12 AWG

Terminal ID: Brass-Hot, Green-Ground, Silver-Neutral

Termination: Back & Side

Product Features

Color: Ivory

Grade: Hospital

NEMA: 5-20R

Standards and Certifications

ANSI: C-73

Applicable Standards: UL 498 and 1310, CSA C22.2 Nos. 42 and 223

Certification/Listing: cCSAus, NOM-ANCE

NEMA: WD-1 & WD-6

Warranty

Product Warranty: 5-Year Limited

Product Lists

[Add to Product List](#)

[View Product List](#)

Support

[TOP](#)

[Product Brochure](#)

Quantity:

[Dimensional Data](#)

[Instruction Sheet](#)

Related Products

[TOP](#)



T5832-HG

Hospital Grade Combination Duplex Receptacle and USB Charger. 20 Amp, 125 Volt, Decora Tamper-Resistan...
[More](#)



T5832-HGE

Hospital Grade Combination Duplex Receptacle and USB Charger. 20 Amp, 125 Volt, Decora Tamper-Resistan...
[More](#)



T5832-HGG

Hospital Grade Combination Duplex Receptacle and USB Charger. 20 Amp, 125 Volt, Decora Tamper-Resistan...
[More](#)

Hospital (Receptac Amp, 125 Resistan...
[More](#)

Videos

[TOP](#)

Hospital Grade USB Charger Duplex Receptacles

Hospital Grade USB Charger Receptacle from Leviton



Hospital Grade USB Charger

ABOUT LEVITON

Leviton is the smart choice, delivering the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial customers in more than 90 countries across the globe. From simple switches and receptacles, to networking systems and smart home automation, Leviton exceeds market needs by delivering innovative products to create sustainable, intelligent environments through its electrical wiring devices, network and

data center connectivity solutions, LED lighting and lighting energy management systems, and security and automation applications. For Leviton, it is clear the FUTURE IS ON.



PRODUCTS

- Connected Home
- Electric Vehicle Charging
- Electrical Wiring Devices
- GFCIs and AFCIs
- Lighting Controls
- Network Solutions
- Security & Automation
- Submetering
- Surge Protective Devices
- Temporary Power

SOLUTIONS

- Applications
- Brands
- Business
- Contech Lighting
- Intense Lighting
- Energy Management
- Government
- Home Solutions
- Industrial
- JCC Lighting Products
- Security & Automation

SUPPORT

- Contact Us
- Cross Reference
- Discussions
- Documents & Resources
- ez-Biz
- ez-Learn
- Knowledgebase
- Leviton Warranties
- Mobile Apps
- Product Support
- Quality Concerns