

## TCR15-W



Color:  White

UPC Code: 07847765538  
Country Of Origin: Mexico  
\*Eligible for ARRA funded projects > \$7,443,000

## TCR15-W

### Brand Features

Plug Into Safety with Leviton Tamper-Resistant (TR) Receptacles. As a long-time manufacturer of tamper-resistant devices, we are pleased to be at the forefront of this safety measure with an expanded product line that encompasses a wide range of TR devices in Residential, Commercial, Industrial and Hospital Grades.

### Item Description

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Tamper-Resistant, Narrow Body Duplex Receptacle, Straight Blade, Commercial Grade, Self Grounding, Side Wired, Steel Strap - WHITE

### Where To Buy

Market Channel

enter your zip code

[Technical Information](#) [Support](#) [Related Products](#)



## Technical Information

TOP



[\\*Disclaimer...](#)

Choose a Color



### Product Lists

[Add to Product List](#)

[View Product List](#)

Quantity:

### AC Horsepower Ratings

**Horsepower Rating:** 1/2 HP

### Electrical Specifications

**Amperage:** 15 Amp  
**Current Limiting:** Full Rated Current  
**Dielectric Voltage:** Withstands 2000V per UL498  
**Grounding:** Self-Grounding

**Pole:** 2  
**Temperature Rise:** Max 30C after 100 cycles OL at 150 percent rated current  
**Voltage:** 125 Volt  
**Wire:** 3

### Environmental Specifications

**Flammability:** Rated V-2 per UL94  
**Operating Temperature:** -40C to 60C

### Material Specifications

**Body Material:** Thermoplastic  
**Face Material:** Thermoplastic  
**Ground Clips:** Brass  
**Grounding Screw:** Plated Steel  
**Line Contacts:** Brass .031 Thick  
**Shutter Mechanism:** Delrin® Acetal  
**Strap Material:** Zinc-Plated Steel  
**Terminal Screws:** Plated Steel

### Mechanical Specifications

**Product ID:** Ratings are permanently marked on device  
**Terminal Accom.:** 10-14 AWG  
**Terminal ID:** Brass-Hot, Green-Ground, Silver-Neutral  
**Termination:** Side  
**Wire Type:** Solid or Stranded Building Wire

### Product Features

**Color:** White

### Standards and Certifications

**ANSI:** C-73  
**cULus:** File E13399  
**NEMA:** WD-1 & WD-6  
**NOM:** 057

### Warranty

**Warranty:** 10-Year Limited

PLEASE READ: TAMPER-RESISTANT NOTICE

Related Products



TCR15

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Tamper-Resistant, Narrow Body Duplex Receptacle, Straight Blade, ... More



TCR15-E

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Tamper-Resistant, Narrow Body Duplex Receptacle, Straight Blade, ... More



TCR15-GY

15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Tamper-Resistant, Narrow Body Duplex Receptacle, Straight Blade, ... More

ABOUT LEVITON

Leviton is the smart choice, delivering the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial customers in more than 90 countries across the globe. From simple switches and receptacles, to networking systems and smart home automation, Leviton exceeds market needs by delivering innovative products to create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, LED lighting and lighting energy management systems, and security and automation applications. For Leviton, it is clear the FUTURE IS ON.



PRODUCTS

- Connected Home
Electric Vehicle Charging
Electrical Wiring Devices
GFCIs and AFCIs
Lighting Controls
Network Solutions
Security & Automation
Submetering
Surge Protective Devices
Temporary Power

SOLUTIONS

- Applications
Brands
Business
Contech Lighting
Intense Lighting
Energy Management
Government
Home Solutions
Industrial
JCC Lighting Products
Security & Automation

SUPPORT

- Contact Us
Cross Reference
Discussions
Documents & Resources
ez-Biz
ez-Learn
Knowledgebase
Leviton Warranties
Mobile Apps
Product Support
Quality Concerns