

LED PAR Series



Stock No.	Product Description
LED-1671-A	PAR30-120-4-28-SW (Soft White)

Description:

Fully encapsulated, 120 Volt, 4 Watt, medium base mounting that integrates energy saving LED technology into a standard PAR30 format.

Available in Soft White (SW).

- Medium screw-in base
- 4 Watt, 120 Volt operation
- Remote transformer not required
- Operates off of standard house current
- Soft White SW (2700K)
- Compare to 35W PAR30 light output
- 28 on-board SMD LED diodes
- Up to 35,000 hour lamp life
- Low heat output
- 2 year warranty
- Not dimmable
- Outdoor rated



Applications:

The PAR30 4W lamp has been designed to retrofit existing PAR30 installations, thereby reducing maintenance and energy expenditures - and as an energy saving light source for new fixtures and installations.

- Retail display applications
- Task lighting
- Recessed downlighting
- Hospitality and institutional outdoor and landscape retrofit
- Underwater fixtures and applications
- Residential lighting

Packaging:

Master pack: 16 lamps



Technical Specifications:

Lamp Type: PAR30	Base Type: E26 Med. Base
Bulb Material: Glass	Input Voltage: AC120V/60Hz
Replaces: 35W	Output Power: 4W
Dimensions: 3-3/4" x 3-1/2"	Beam Angle: 110°
Light Source: 28pc SMD LED	Color: (SW) est. 2700K
Dimmable: No	
CRI: 70	Lumens / Watt: 65
Lumens: 250(SW)	Life Time: Up to 35,000 Hrs.
UV / IR Radiation: No	Inert Gasses: No

Note: All specification information falls within a ± 2% range

NOTE: Light Emitting Designs is providing this information to the general public. Please note that all products contained herein are trademarked, copyrighted, and/or have patents pending. Any use of these designs is strictly prohibited without prior written consent. Light Emitting Designs protects its proprietary information vigorously in the courts of the United States of America.

