

## ■ Lithonia General-Purpose T8 Troffers

- Low-profile design is optimized for T8 lamps and low-profile electronic ballasts
- Ideal for restricted plenum applications

Mfr.'s Model No.	No. Lamps	Lamp Type
2GT82U316A12MVOLTGEB10IS	2	32T8U/15/8
2GT8232A12MVOLTGEB10IS	2	32T8
2GT8432A12MVOLT1/4GEB10ISPWS1836LP735	4	32T8
2GT8332A12MVOLT1/3GEB10IS	3	32T8
2GT8432A12MVOLT1/4GEB10IS	4	32T8

Applications

- High-efficiency fixture helps reduce energy costs

Voltage	Ballast Type	Lens Type	Air Function	Dimensions (ft.)
120-277	Electronic	Acrylic #12	Static	2 x 2
120-277	Electronic	Acrylic #12	Static	2 x 4
120-277	Electronic, ¼	Acrylic #12	Static	2 x 4
120-277	Electronic, ½	Acrylic #12	Static	2 x 4
120-277	Electronic, ¾	Acrylic #12	Static	2 x 4