

FEATURES & SPECIFICATIONS

INTENDED USE

Highly energy-efficient lighting that is ideal for signs, entry monuments, residential facades and landscaping. **Certain airborne contaminants can diminish integrity of acrylic.** [Click here for Acrylic Environmental Compatibility table for suitable uses.](#)

CONSTRUCTION

Compact, rugged, die-cast aluminum housing is ribbed for strength and cool operation. F500QL lens attaches via tool-less clips. F13L, F213L, F500QLD, and F1500QD door frame is die-cast aluminum with tool-less latch closure. FP213 is polycarbonate.

Bronze polyester powder paint for lasting durability.

OPTICAL SYSTEM

Anodized aluminum reflector with high efficiency and wide beam spread. Tempered glass lens with high temperature gasketing to inhibit entrance of external contaminants.

120V, 13W (for CFL) or 500W (for quartz) lamp included. Double-ended 1500W voltage determined by lamp (not included).

13W twin-tube compact fluorescent lamp(s) included in carton.

INSTALLATION

Adjustable mounting knuckle with 1/2" NPS threaded stem mounts to standard outlet boxes.

LISTING

UL/CUL listed for wet locations.

WARRANTY

Fixtures are covered by Lithonia Lighting 24-month warranty against mechanical defects in manufacture.

Catalog Number
Notes
Type

Contractor Select

Flood Lighting




F213L


13W Compact Fluorescent
500W Quartz



FP213L



F213L/F500



FP213L

All dimensions are inches (centimeters).

ORDERING INFORMATION

Catalog Number	UPC	Description	Wattage	Lamp Source	# of Lamps	Voltage	Finish	Lamps Included	Approx. Weight (lbs)	Pallet Qty	Standard Carton Qty
F13L 120 M12	745973505304	Die-cast floodlight	13	Fluorescent	1	120	Dark bronze	Y	6	240	12
FP213L 120 M12	745973817902	Polycarbonate floodlight	13	Fluorescent	2	120	Dark bronze	Y	2	288	12
F213L 120 M12	745973505175	Die-cast floodlight	13	Fluorescent	2	120	Dark bronze	Y	6	240	12
F500QL 120 M12	745973505557	Die-cast floodlight	500	Quartz	1	120	Dark bronze	Y	3	240	12
F500QLD 120 M12	745973505533	Die-cast floodlight	500	Quartz	1	120	Dark bronze	Y	3	240	12