

PRODUCT INFORMATION

FLOODLIGHTS



Intended Use

Floodlight for commercial or residential signs, entry monuments or facades. HID, quartz, and compact fluorescent sources.

Construction

Rugged, die-cast aluminum housing is ribbed for maximum heat dissipation. Die-cast aluminum doorframes. F500QL lens attaches with clips. FP is polycarbonate. Finish is dark

Optics

Anodized aluminum reflectors with high efficiency and wide beam spread. F150MSL features a spot distribution.

Electrical

120 volt reactor, normal power factor for 50-150 HPS and 70-100MH. Quad tap, high reactance, high power factor for 150M. Medium base socket.
Quad tap, super CWA for 250M and 400M. Mogul-base socket.

120V for 13W (for CFL) or 500W (for quartz). Lamps included. 13W compact fluorescent lamp is a twin-tube.

Double-ended 1500W voltage determined by lamp (not included).

Installation

Floodlights feature adjustable mounting knuckle with 1/2" NPS threaded stem. Mounts to standard outlet boxes. Medium floods (250M and 400M) are yoke mount.

Listings

Listed and labeled to UL standards for wet locations. Listed and labeled to CSA standards. 25°C maximum ambient temperature. Fixtures are covered by Lithonia Lighting 12-month warranty against mechanical defects in manufacture.



ORDERING INFORMATION

CATALOG NUMBER	DESCRIPTION	WATTAGE	LAMP TYPE	VOLTAGE	FINISH	LAMP INCLUDED	APPROX. WEIGHT (LBS)	STANDARD CARTON QTY.
F50SL 120 M6	Micro floodlight	50S	HPS	120	Dark bronze	Y	7	6
F70SL 120 M6	Micro floodlight	70S	HPS	120	Dark bronze	Y	7	6
F100SL 120 M6	Micro floodlight	100S	HPS	120	Dark bronze	Y	7	6
F150SL 120 M6	Micro floodlight	150S	HPS	120	Dark bronze	Y	7	6
F70ML 120 M6	Micro floodlight	70M	MH	120	Dark bronze	Y	7	6
F100ML 120 M6	Micro floodlight	100M	MH	120	Dark bronze	Y	7	6
F150ML M4	Small floodlight	150M	MH	120/208/240/277	Dark bronze	Y	14	4
F150MSL M4	Spot, small floodlight	150M	MH	120/208/240/277	Dark bronze	Y	14	4
F250ML SCWA	Medium floodlight	250M	MH	120/208/240/277	Dark bronze	Y	29	1
F400ML SCWA	Medium floodlight	400M	MH	120/208/240/277	Dark bronze	Y	29	1
F13L 120 M12	Cast-glass floodlight	13	CFL	120	Dark bronze	Y	6	12
F213L 120 M12	Cast-glass floodlight	13	CFL	120	Dark bronze	Y	6	12
FP213L 120 M12	Polycarbonate floodlight	13	CFL	120	Dark bronze	Y	2	12
F500QL 120 M12	Cast-glass floodlight	500Q	Quartz	120	Dark bronze	Y	3	12
F500QLD 120 M12	Cast-glass floodlight	500Q	Quartz	120	Dark bronze	Y	3	12
F1500QD M6	Cast-glass floodlight	1500Q	Quartz	--	Dark bronze	N	6	6

ADDITIONAL INFORMATION

For additional product information, visit www.lithonia.com.

Drawings are for dimensional detail only and may not represent actual mechanical configuration. Dimensions are shown in inches (centimeters) unless otherwise noted.

