



Representative

Catalog Number: TR65
Product ID: 7TAA267170R0025
UPC Number: 78378610148
Status: Active

Aluminum 6 inch Service Entrance Compression Splice for Wire Range 1 ASCR, 1/0 Str., Yellow, Die: 5/8

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Service Entrance Connector
Special Features	Contains Oxide Inhibiting Compound
Application	Semi-tension Splice used for Service Entrance on Commercial-Industrial Loads
Standard	Passes the requirements of ANSI C119.4
Size	6 inch
Connection	Crimp/ Compression
Conductor Range	1 ASCR, 1/0 Stranded.
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

Packaging

Inner Quantity	50
Inner Dimensions (inches)	7.2x5.1x6.5
Outer Quantity	300
Outer Dimensions (inches)	20.5x11.25x7.7
Weight Uom	13 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com