



FE3200 Series

[View larger image](#)



[Description](#) [Features](#) [Replacement Parts](#) [Send to friend](#) [Tags](#)

A non-conductive fiberglass industrial extension ladder with 300lbs. duty rating.

The ladders features outside slide guides, D-shape rungs fully serrated for slip resistant surface, non marring rail end caps, QuickLatch rung lock for better secure operation and swivel safety shoes to be usee as tread down or in spike position.

Find our ladders near you:

[SEARCH LOCAL DISTRIBUTORS](#)

Model	Ladder Size (ft)	Duty Rating	Load Capacity (Lbs)	Approx. Weight (lbs)	Length Each Section (ft)	Approx. Cubes (ft)	Max ext. Length (ft)	Max. Outside Width (In)
FE3118 BUY NOW ★★★★★ ★★★★★ Reviews / Rate	18	IA	300	41	18	7.5	18	17 1/16
FE3120 BUY NOW ★★★★★ ★★★★★ Reviews / Rate	20	IA	300	45	20	11.4	20	17 1/16
FE3216 BUY NOW ★★★★★ ★★★★★ Reviews / Rate	16	IA	300	30	8	6.5	13	17 1/16
FE3220 BUY NOW ★★★★★ ★★★★★ Reviews / Rate	20	IA	300	42	10	8.6	17	17 1/16