



[View larger image](#)

## FS1500 Series

[Description](#)   [Features](#)   [Replacement Parts](#)   [Send to friend](#)   [Tags](#)

A non-conductive fiberglass step ladder extra-heavy duty capable of supporting 300lbs.

Equipped with Da Boot for slip resistant footing, SHOX system and the ProTop, a non-conductive structural molded top with hardware tray, paint can holder, handyman's tool slots, pipe holder, curved front of top provides leg comfort and convenient magnet to secure small steel parts.








The FS1500 Series receives a 5-Star Rating! **Read what customers had to say.**

Find our ladders near you:

[SEARCH LOCAL DISTRIBUTORS](#)

Model	Ladder Size (Ft)	Duty Rating	Load Capacity (Lbs)	Step Size	Bottom Width (In.)	Approx. Spread (In.)	Approx. Weight (Lbs)	Actual Cubic Ft. (ft³)
FS1502 <a href="#">BUY NOW</a> ★★★★★ ★★★★★ 5 out of 5 stars. Reviews / Rate	2	IA	300	3"	17	18 1/4	8	1.8
FS1503 <a href="#">BUY NOW</a> ★★★★★ ★★★★★ Reviews / Rate	3	IA	300	3"	18 1/16	23	12	2.6
FS1504 <a href="#">BUY NOW</a> ★★★★★ ★★★★★ Reviews / Rate	4	IA	300	3"	19 9/16	28 15/16	14	3.6
FS1505 <a href="#">BUY NOW</a> ★★★★★ ★★★★★	5	IA	300	3"	21 1/16	34 7/8	17	4.9

Reviews / Rate									
FS1506  ★★★★★ ★★★★★	6	IA	300	3"	22 9/16	40 7/8	20	5.7	
Reviews / Rate									
FS1507  ★★★★★ ★★★★★	7	IA	300	3"	24 1/16	46 13/16	22	7.9	
Reviews / Rate									
FS1508  ★★★★★ ★★★★★	8	IA	300	3"	25 9/16	52 3/4	26	8.7	
Reviews / Rate									
FS1510  ★★★★★ ★★★★★	10	IA	300	3"	28 9/16	64 11/16	34	10.9	
Reviews / Rate									
FS1512  ★★★★★ ★★★★★	12	IA	300	3"	31 9/16	76 1/16	47	15.9	
Reviews / Rate									