

# FLUORESCENT SOCKETS

ALL NEW LEVITOR PRODUCTS



**2G11 FLUORESCENT SOCKET**  
 2G11 BASE • SLIDE-ON  
 BACK MOUNT STYLE SOCKET  
 RATED 660W-600V  
**D3508**



**NON-DIMMABLE BALLAST  
 2G11 FLUORESCENT SOCKET**  
 2G11 BASE  
 BACK MOUNT HAS MOUNTING FEET  
 24MM ON CENTER  
 PUSH-IN TERMINALS  
 RATED 75W-600V  
**D3936**



**2G11 VERTICAL MOUNT  
 FLUORESCENT SOCKET**  
 2G11 BASE  
 PUSH-IN TERMINALS  
 RATED 75W-600V  
**D3937**



**PLASTIC SNAP-IN  
 2G11 LAMP SUPPORT**  
**D3610**



**PLASTIC SCREW-DOWN  
 2G11 LAMP SUPPORT**  
**D3612**



**LAMP SUPPORT BRACKET**  
 FOR 2G11 TUBE  
 3 HEIGHT ADJUSTMENTS:  
 21, 24 & 27MM  
 UV STABILIZED • CLEAR  
**D3939**  
*(MUST BE USED WITH D3938)*



**LAMP SUPPORT BRACKET**  
 FOR 5, 7, 9 & 13W G23 BASE LAMPS  
 3 HEIGHT ADJUSTMENTS:  
 17.5, 20.5 & 23.5MM  
 UV STABILIZED • CLEAR  
**D3940**  
*(MUST BE USED WITH D3938)*



**LAMP SUPPORT BRACKET**  
 FOR 2G11 TUBE  
 RAISES LAMP 15.5MM  
 SNAP IN BRACKET FOR  
 5.5MM CUTOUT  
**D3958**



**CIRCLINE CLIP**  
 FOR MOUNTING CIRCLINE  
 LAMPS TO PANS  
**B963**



**LAMP SUPPORT FOOT**  
 SNAP-IN FOOT FOR D3939 & D3940  
 DIAMETER 5.5MM  
 CUT-OUT FOR WALL THICKNESS  
 UP TO 1MM  
**D3938**

