



## Hi-lume® Ballast Models

Lamp Type				120 VOLTS		277 VOLTS	
	Lamp Watts (length)	Lamps per ballast	Case Type	Ballast Current (A)	Hi-lume® Model Number	Ballast Current (A)	Hi-lume® Model Number
<b>T4 Triple-tube 4-pin</b>  1/2 in (12.7 mm) diameter	26 W	1	A	0.30	HL3-T426-120-1-S <sup>1</sup>	0.11	HL3-T426-277-1-S <sup>1</sup>
	32 W	1	A	0.35	HL3-T432-120-1-S <sup>1</sup>	0.13	HL3-T432-277-1-S <sup>1</sup>
<b>T5-HO Linear High Output</b>  5/8 in (15.875 mm) diameter	24 W [21.5 in (546 mm)]	1 2	C C	0.31 0.62	FDB-T524-120-1 FDB-T524-120-2	0.15 0.24	FDB-T524-277-1 FDB-T524-277-2
	39 W [33.4 in (848 mm)]	1 2	C C	0.38 0.76	FDB-T539-120-1 FDB-T539-120-2	0.19 0.32	FDB-T539-277-1 FDB-T539-277-2
	54 W [45.2 in (1148 mm)]	1 2	C C	0.58 1.1	FDB-T554-120-1 FDB-T554-120-2	0.25 0.45	FDB-T554-277-1 FDB-T554-277-2

<sup>1</sup> Mounting studs standard for T4 ballasts. Delete suffix -S in the model number if mounting studs not needed.

Job Name:	Model Numbers:
Job Number:	